PocketMonitor





Ra Ra	aw beam	TOWENHANGE	20 VV - 12 KVV	
Pc	ower	BEAM QUALITY M ²	Everything is possible – application is only power density dependant	
Be	eam profile	BEAM DIAMETER	Up to 36 mm	
Po	pinting stability	HIGHLIGHT	Separate absorber	
Ve	ctor	INTERFACE	Display screen	
)(‡ Fo	ocus shift			

Tech Corner

The PocketMonitor (PMT) calculates the energy of a laser pulse by determining the temperature changes within its absorber. The length of the laser pulse measured can be between 10-20 seconds. The accurate effective laser power is based on calculations resulting from the temperature curves of absorbing tool. The system is suitable for CO_2 and NIR (800 – 1100 nm) laser radiation with respective calibration.

The PocketMonitor is a mobile, easy-to-use power meter developed specifically for everyday use in service and production. It is sure to impress with its compact, durable design as well as its fast and uncomplicated operation. A full aluminum casing protects sensitive electronics from shocks and moisture. When folded together, the absorber protects operating elements from undesired damages.

PocketMonitor must be air/water cooled and dried between consecutive measurements.

Models & Options

- 1 Four absorber versions for different power ranges: PocketMonitors 70icu or 120icu with a copper cone (icu) are designed for the highest power ranges. Lower power ranges can be masured with 05p and 30p variants.
- 2 When it comes to choosing a suitable device, the power density is often just as important as the maximum power. Especially high power reserves are offered by PMT 70icu and PMT 120icu, that can be used for laser powers up to 5 kW/cm².
- 3 All models are also available with a cableconnected absorber with various cable lengths.



- 4 PocketMonitors PMT70 and PMT120 are also available with silver coated cones (iag) for higher energy density measurements in the NIR range. Such applications can be individually discussed with PRIMES.
- 5 We recommend having a suitable case for safe transport and storage.

MEASUREMENT PARAMETERS	PMT 05p	PMT 30p	PMT 70icu	PMT 120icu	
Power range	25 W – 500 W	150 W – 3000 W	350 W – 7 000 W	500 W – 12000 W	
Wavelength range	800 - 1100 nm or 10.6 µm	800 - 1100 nm or 10.6 μm	800 - 1100 nm or 10.6 µm	800 - 1100 nm or 10.6 μm	
Max. beam diameter on the absorber	27.5 mm	48 mm	36 mm	36 mm	
Max. power density on the absorber (inlet aperture) at < 1 kW at < 3 kW at 5 kW	2.5 kW/cm² - -	2.5 kW/cm² 1.5 kW/cm² –	5 kW/cm ² 5 kW/cm ² 5 kW/cm ²	5 kW/cm² 5 kW/cm² 5 kW/cm²	
Irradiation time	10 s (at maximum permissible laser power),10 s (at maximum permissible laser power)20 s (at 50 % of the maximum permissible laser power)				
DEVICE PARAMETERS					
Max. angle of incidence perpendicular to inlet aperture	± 5 °	±5°	±5°	±5°	
Max. centered tolerance	± 2.0 mm	± 2.0 mm	± 2.0 mm	± 2.0 mm	
Measuring accuracy	±4%	±4%	±4%	±4%	
Reproducibility					
	±2%	± 2 %	±2%	± 2 %	
DIMENSIONS AND WEIGHT	± 2 %	±2%	±2%	±2%	
DIMENSIONS AND WEIGHT	± 2 % 45 mm	± 2 % 79 mm	± 2 % 79 mm	± 2 % 99 mm	
DIMENSIONS AND WEIGHT Absorber diameter Absorber height	± 2 % 45 mm 15 mm	± 2 % 79 mm 20 mm	± 2 % 79 mm 75 mm	± 2 % 99 mm 75 mm	



System description: The PocketMonitor (PMT) is a compact and precise laser power meter that utilizes a proven calorimetric measurement principle. It offers high accuracy of +/-4 % and is designed to measure both continuous wave (CW) and pulsed laser systems. The PMT is suitable for lasers operating in the near-infrared (NIR) and CO₂ wavelength ranges.

Your benefit: Thanks to it's robust and compact design, the PocketMonitor is a costeffective and reliable tool that fits easily in service boxes. The display not only shows all the information at a glance, but can provide even more parameters with the press of a button.

CONCLUSION

The power measurement for CO_2 and NIR lasers can be ensured by the robust and reliable PocketMonitor.



PRIMES GmbH | Max-Planck-Straße 2 | 64319 Pfungstadt | Germany | www.primes.de Version: 7.0 EN - 10_2024 | Specifications subject to change without further notice.

